



# ProBleacher™

## Specifications

Power Input 110-120V / 220-240V

Frequency 50-60 Hz

Ambient Temperature 10-30°C / 50-86°F

Relative Humidity 30-70% (non-condensing)

LED Output 36 Watts (4X9W)

LED Wavelength 450/500nm

Unit Size 12 x 12 x 10.25in  
(300 x 300 x 260 mm)  
22lbs  
(10Kg)

Chamber Size 12 x 12 x 6.25in  
(300 x 300 x 160 mm)

Shipping Size 17 x 17 x 16in  
(43 x 43 x 40cm)  
25lbs  
(12Kg)

### Stratasys Headquarters

7665 Commerce Way,  
Eden Prairie, MN 55344  
+1 800 801 6491 (US Toll Free)  
+1 952 937-3000 (Intl)  
+1 952 937-0070 (Fax)

1 Holtzman St., Science Park,  
PO Box 2496  
Rehovot 76124, Israel  
+972 74 745 4000  
+972 74 745 5000 (Fax)

[stratasys.com](http://stratasys.com)

ISO 9001:2015 Certified

© 2021 Stratasys Ltd. All rights reserved. Stratasys, Stratasys signet, ProBleacher are trademarks or registered trademarks of Stratasys Ltd. and/or its subsidiaries or affiliates and may be registered in certain jurisdictions. All other trademarks belong to their respective owners. Product specifications subject to change without notice. PSS\_PJ\_ProBleacher\_0821a

